

YA8CL1BRBOX500

by Burndy
Catalog ID: YA8CL1BRBOX500

COPPER COMPRESSION TERMINAL.



Product Details

General

Color Code	Red
Connector Type	Terminal
Die Index	49
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810192344
UPC 12 Digit	7818101923444

Dimensions

Dimension - B Length inch	0.44 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - D inch	0.58 in
Dimension - Hole Size inch	0.58 in
Dimension - Hole Size mm	15 mm
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.26 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.44 in
Dimension - Stud Size inch	#8
Dimension - Z inch	0.33 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Solid Size	6 AWG
Conductor - Copper Solid Size Range	6 AWG
Conductor - Copper Str Navy Size	23 (7) Navy
Conductor - Copper Str Navy Size Range	23 (7) Navy
Conductor - Copper Str Size	8 AWG
Conductor - Copper Str Size Range	8 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	500
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)