

# YA8CLNK

by Burndy  
Catalog ID: YA8CLNK

Prop 65 Notice

Cu Tubing Compression Terminal, 1 Hole W/InspWindow, #8 AWG #6 Sol. Code, 23 Navy, 600V - 35kV, #8 - #10 stud, Nickel Plated



## Product Details

### General

Color Code	Red
Connector Type	Terminal
Die Index	49
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Nickel
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Nickel Plated
UPC	781810069592
UPC 12 Digit	7818100695922

### Dimensions

Dimension - B Length inch	0.44 in
Dimension - Bolt Hole Size inch	0.20 in
Dimension - D inch	0.48 in
Dimension - Hole Size inch	0.21 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.16 in
Dimension - N inch	0.22 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.41 in
Dimension - Strip Length inch	7/16
Dimension - Z inch	0.26 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Solid Size	6 AWG
Conductor - Copper Solid Size Range	6 AWG
Conductor - Copper Str Navy Size	23 (7) Navy
Conductor - Copper Str Navy Size Range	23 (7) Navy
Conductor - Copper Str Size	8 AWG
Conductor - Copper Str Size Range	8 AWG
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	50
-----------------------	----

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)