



## YA8CLNT6

by Burndy  
Catalog ID: YA8CLNT6

Prop 65 Notice

Flex Conductor Standard Barrel Narrow, #8 AWG, 6, 1.08 in L.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available

## Product Details

### General

Application	For Code Conductor
Color Code	Red
Connector Type	Terminal
Die Index	49
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YA-L-NT
UPC	781810034309

### Dimensions

Dimension - B Length fraction	7/16 in
Dimension - B Length inch	0.44 in
Dimension - D inch	0.41 in
Dimension - Inside Diameter inch	0.18 in
Dimension - L Length Overall mm	27 mm
Dimension - Length Overall inch	1.08 in
Dimension - N inch	0.19 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.29 in
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	#6
Dimension - Z inch	0.22 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	8 AWG
Conductor - Copper Str Size Range	8 AWG

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)