

# YAAKIT2

by Burndy  
Catalog ID: YAAKIT2

Prop 65 Notice

Transformer Lug Kit, 2/0 AWG-300 kcmil



## Product Details

### General

Color Code	Blue
Connector Type	Terminal
Die Index	470
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
UPC	781810033487
UPC 12 Digit	7818100334877

### Dimensions

Dimension - B Length inch	1.53 in
Dimension - D inch	1.37 in
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	99 mm
Dimension - Length Overall inch	3.90 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.01 in
Dimension - Pad Width inch	1.38 in
Dimension - Z inch	0.74 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - AL Str Size	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil
Conductor - AL Str Size Range	2/0 AWG-300 kcmil
Conductor - Copper Str Size	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil
Conductor - Copper Str Size Range	2/0 AWG-300 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
Package Contents	(8) YA30-7;(8) 1/2-20 x 3/4 in, (8) 1/4-20x2 in HEB Bolt;(16) 1/4-20 HN Nut;Captive to Nut

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)