



YAB28CG24

by Burndy
Catalog ID: YAB28CG24

Prop 65 Notice

One hole Cu Tubing Compression Terminal 3 inches long

Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	621945125858
UPC 12 Digit	6219451258588

Dimensions

Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	1.66 in
Dimension - D inch	2.25 in
Dimension - Hole Size inch	0.34 in
Dimension - Hole Size mm	9 mm
Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	3.00 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	0.77 in
Dimension - Pad Width inch	1.00 in
Dimension - Z inch	0.75 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	4/0 (550/#24) DLO
Conductor - Copper DLO Size Range	4/0 (550/#24) DLO
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)