



YAB28CG41

by Burndy
Catalog ID: YAB28CG41

LUG 4/OEFLX K=.44 E=1.0

Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	621945211087
UPC 12 Digit	6219452110877

Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.61 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	2.50 in
Dimension - Hole Size inch	0.44 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	107 mm
Dimension - Length Overall inch	4.21 in
Dimension - N inch	0.44 in
Dimension - Outside Diameter inch	0.81 in
Dimension - Pad Width inch	1.00 in
Dimension - Strip Length inch	1-3/8
Dimension - Thread Size	3/8
Dimension - Z inch	1.06 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size	4/0 AWG
Conductor - Copper Flex G Size Range	4/0 AWG
Conductor - Copper Flex H Size	4/0 AWG
Conductor - Copper Flex H Size Range	4/0 AWG
Conductor - Copper Flex I Size	4/0 AWG
Conductor - Copper Flex I Size Range	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
Conductor - Copper Flex K Size Range	4/0 AWG
Conductor - Copper Flex M Size	4/0 AWG
Conductor - Copper Flex M Size Range	4/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)