



YAB28CG53

by Burndy
Catalog ID: YAB28CG53

Prop 65 Notice

Cast Lug; 4/0 Flex; M8 Stud Hole

Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810468333
UPC 12 Digit	7818104683333

Dimensions

Dimension - B Length inch	1.28 in
Dimension - D inch	1.25 in
Dimension - Hole Size inch	0.34 in
Dimension - Hole Size mm	9 mm
Dimension - L Length Overall mm	82 mm
Dimension - Length Overall inch	3.22 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.77 in
Dimension - Pad Width inch	1.19 in
Dimension - Strip Length inch	1-1/2
Dimension - Z inch	0.62 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Solid Size	4/0 AWG
Conductor - Copper Solid Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)