



YAB2C2LH75

by Burndy
Catalog ID: YAB2C2LH75

Prop 65 Notice

Copper Hysealug, 2 Pad Holes, 2 Str.

Product Details

General

| | |
|--------------------------------------|-----------------------------|
| Connector Type | Terminal |
| Feature - Barrel Style | Shrouded |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 2 |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Temperature Rating | 194 |
| Trade Name | HYSEALUG™ |
| Type | Shrouded Barrel, Tin Plated |
| UPC | 781810506479 |
| UPC 12 Digit | 7818105064799 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length inch | 2.59 in |
| Dimension - D inch | 3.01 in |
| Dimension - Inside Diameter inch | 0.91 in |
| Dimension - L Length Overall mm | 165 mm |
| Dimension - Length BB inch | 0.75 in |
| Dimension - Length Overall inch | 6.50 in |
| Dimension - N inch | 0.63 in |
| Dimension - Pad Width inch | 0.75 in |
| Dimension - Z inch | 0.63 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|-----------------------------|-------|
| Conductor - Copper Str Size | 2 AWG |
|-----------------------------|-------|

| | |
|-----------------------------------|--------|
| Conductor - Copper Str Size Range | 2 AWG |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 25 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)