



## YAB6CCG8

by Burndy  
Catalog ID: YAB6CCG8

Prop 65 Notice

CAST LUG 6 FLEX

## Product Details

### General

Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	621945332492
UPC 12 Digit	6219453324922

### Dimensions

Dimension - B Length inch	0.94 in
Dimension - D inch	1.63 in
Dimension - Hole Size inch	0.36 in
Dimension - Hole Size mm	9 mm
Dimension - L Length Overall mm	73 mm
Dimension - Length Overall inch	2.88 in
Dimension - N inch	0.38 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Pad Width inch	0.59 in
Dimension - Z inch	0.36 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Flex G Size	6 AWG
Conductor - Copper Flex H Size	6 AWG
Conductor - Copper Flex I Size	6 AWG
Conductor - Copper Flex K Size	6 AWG
Conductor - Copper Flex M Size	6 AWG
Conductor - Copper Flex M Size Range	6 AWG
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	10
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)