



YAD1010F

by Burndy
Catalog ID: YAD1010F

Prop 65 Notice

Copper Compression Lug, Fork Tongue, w/ Inspection Hole, 14-10 AWG, #8-#10 Stud, Long Barrel, Tin Plated.

Features: The Fork Permits Rapid Installation Of The Terminal Under A Screw Head Without Completely Removing The Screw, Two Or More Terminals May Be Stacked Easily On A Common Stud, Wire Strip Length: 11/32 IN, Finish: Electro-Tin Plated, Package: Bulk, Installation Tool: Non-Ratchet: Y10D, Y10-22 Tool, Ratchet: Y8MRB-1, MR20, MR8G98 Tool

Product Details

General

| | |
|-------------|------------------------------------|
| Application | For Use in compression connections |
| Sub Brand | HYLUG |
| Type | Fork Tongue |
| UPC | 781810806401 |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-----|
| Minimum Pack Quantity | 500 |
|-----------------------|-----|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)