



YAE10N3M

by Burndy
Catalog ID: YAE10N3M

Prop 65 Notice

TERMINAL-NYLON INSULATED, RING-TONGUE MULTI-FINGER INSULATION GRIP.

Product Details

General

Color Code	Yellow
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	INSULUG™
UPC	781810028483
UPC 12 Digit	7818100284833

Dimensions

Dimension - Hole Size fraction	10/37
Dimension - Hole Size inch	0.27 in
Dimension - Length Overall inch	1.39 in
Dimension - Pad Width inch	0.54 in
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.44 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 12;AN 10
Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)