



YAE10N44M

by Burndy
Catalog ID: YAE10N44M

Prop 65 Notice

Nylon Insulated Cu Terminal, Ring Tongue, AN 12 - 10, #4 - #6 stud, Yellow

Product Details

General

Color Code	Yellow
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	INSULUG™
UPC	781810028490
UPC 12 Digit	7818100284900

Dimensions

Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Length Overall inch	1.10 in
Dimension - Pad Width inch	0.28 in
Dimension - Stud Size inch	#4 - #6
Dimension - Z inch	0.29 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 12;AN 10
Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
Packaging Type	Reel

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)