



YAE10N4BOX

by Burndy
Catalog ID: YAE10N4BOX

Prop 65 Notice

Insulated Copper Terminal, 3/8" Stud, 1.39 in L, .54 in W, Tin Plated, 300 Volts Max.

Product Details

General

Color Code	Yellow
Connector Type	Terminal
Insulation	Y
Insulation Type	Nylon
Material	Copper
Military Specification	MS25036
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Temperature Rating	105°C
Trade Name	INSULUG™
UPC	781810046029
UPC 12 Digit	7818100460299

Dimensions

Dimension - Hole Size fraction	23/59
Dimension - Hole Size inch	0.39 in
Dimension - L Length Overall mm	35 mm
Dimension - Length Overall inch	1.39 in
Dimension - Pad Width inch	0.54 in
Dimension - Strip Length inch	3/8 in
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.44 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">• UL486• Military Specified (Mil-Spec)
Standards - Industry Standards Met	<ul style="list-style-type: none">• UL486• Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)