



## YAE10NM

by Burndy  
Catalog ID: YAE10NM

Prop 65 Notice

Terminal - Nylon Insulated, Ring Tongue Multi-Finger Insulation Grip, 12 AWG - 10 AWG, #8-#10 stud, Tin Plated, Reel Packaging

## Product Details

### General

Application	Power Connector
Color Code	Yellow
Connector Type	Ring Terminal
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring Terminal
Plated	Y
Plating Type	Tin
Temperature Rating	105° C
Trade Name	INSULUG™
UPC	781810028650
UPC 12 Digit	7818100286500

### Dimensions

Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	#8-#10
Dimension - Length Overall inch	1.15 in
Dimension - N inch	0.19 in
Dimension - Pad Width inch	0.38 in
Dimension - Strip Length inch	3/8 in
Dimension - Stud Size inch	#8 - #10
Dimension - Z inch	0.28 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - Copper Str Size Range	12 AWG - 10 AWG
-----------------------------------	-----------------

Conductor Type	CU C Str-Size
----------------	---------------

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"><li>• UL486</li><li>• Military Specified (Mil-Spec)</li></ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"><li>• UL486</li><li>• Military Specified (Mil-Spec)</li></ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1000
Packaging Type	Reel

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)