

YAE12N14

by Burndy
Catalog ID: YAE12N14

Prop 65 Notice

Terminal - Nylon Insulated, Ring Tongue Multi-Finger Insulation Grip, 14 AWG - 12 AWG, #4-#6 stud, Tin Plated, Bulk Packaging



Product Details

General

Color Code	Green
Connector Type	Ring Terminal
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring Terminal
Plated	Y
Plating Type	Tin
Temperature Rating	105° C
Trade Name	INSULUG™
UPC	781810550502
UPC 12 Digit	7818105505022

Dimensions

Dimension - Length Overall inch	1.023 in
Dimension - Pad Width inch	0.25 in
Dimension - Strip Length inch	21/64 in
Dimension - Stud Size inch	#4 - #6
Dimension - Z inch	0.286 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size Range	14 AWG - 12 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">• UL486• Military Specified (Mil-Spec)
Standards - Industry Standards Met	<ul style="list-style-type: none">• UL486• Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
Packaging Type	Bulk

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)