

YAE14N108LFBOX

by Burndy
Catalog ID: YAE14N108LFBOX

Snap Fork Tongue, 16 AWG - 14 AWG, .93 in L.

Features: Locking Fork Tongue, Rapid easy installation of terminal without complete removal of screw



Product Details

General

Application	Power Connector
Color Code	Blue
Connector Type	Locking Fork Terminal
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Locking Fork
Plated	Y
Plating Type	Unplated
Sub Brand	INSULUG
Temperature Rating	105° C
Trade Name	INSULUG™
Type	Long Barrel
UPC	781810524541
UPC 12 Digit	7818105245411

Dimensions

Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in
Dimension - Pad Width inch	0.30 in
Dimension - Strip Length inch	7/32 in
Dimension - Stud Size fraction	#6;#8
Dimension - Stud Size inch	#6 - #8
Dimension - Z inch	0.30 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)