

# YAE14N1BOX90

by Burndy  
Catalog ID: YAE14N1BOX90

Prop 65 Notice

Nylon insulated multi finger right angled ring terminal 14 AWG wire size,  
#6-#8 stud size



## Product Details

### General

Color Code	Blue
Connector Type	Terminal
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	INSULUG™
UPC	781810542422
UPC 12 Digit	7818105424222

### Dimensions

Dimension - L Length Overall mm	12.45 mm
Dimension - Length Overall inch	0.49 in
Dimension - Stud Size inch	#6 - #8
Dimension - Width inch	0.31 in
Dimension - Width mm	7.87 mm
Dimension - Z inch	0.28 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - Copper Solid Size	14 sol.
Conductor - Copper Str Size	14 str.
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL486</li> <li>• Military Specified (Mil-Spec)</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL486</li> <li>• Military Specified (Mil-Spec)</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)