



YAE14NM

by Burndy
Catalog ID: YAE14NM

Prop 65 Notice

Terminal - Nylon Insulated, Ring Tongue Multi-Finger Insulation Grip, 16 AWG- 14 AWG, #8-#10, Tin Plated, Reel Packaging

Product Details

General

| | |
|--------------------------------------|---------------|
| Color Code | Blue |
| Connector Type | Ring Terminal |
| Feature - Barrel Style | Shrouded |
| Feature - Barrel Type | Standard |
| Insulation | Y |
| Insulation Type | Nylon |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Physical Attribute - Tongue Type | Ring Terminal |
| Plated | Y |
| Plating Type | Tin |
| Temperature Rating | 105° C |
| Trade Name | INSULUG™ |
| UPC | 781810028681 |
| UPC 12 Digit | 7818100286811 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - Hole Size fraction | 1/5 |
| Dimension - Hole Size inch | 0.20 in |
| Dimension - Length Overall inch | 0.92 in |
| Dimension - N inch | 0.16 in |
| Dimension - Pad Width inch | 0.31 in |
| Dimension - Strip Length inch | 3/16 in |
| Dimension - Stud Size inch | #8 - #10 |
| Dimension - Width inch | 0.09 in |
| Dimension - Z inch | 0.28 in |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

Conductor Related

| | |
|-----------------------------------|-----------------|
| Conductor - Copper Str Size Range | 16 AWG - 14 AWG |
|-----------------------------------|-----------------|

| | |
|----------------|---------------|
| Conductor Type | CU C Str-Size |
|----------------|---------------|

Certifications and Compliance

| | |
|------------------------------------|---|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | <ul style="list-style-type: none">• UL486• Military Specified (Mil-Spec) |
| Standards - Industry Standards Met | <ul style="list-style-type: none">• UL486• Military Specified (Mil-Spec) |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|------|
| Minimum Pack Quantity | 2000 |
| Packaging Type | Reel |

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)