



## YAE18Z2

by Burndy  
Catalog ID: YAE18Z2

Prop 65 Notice

Copper Lug, Fork Tongue, w/ Inspection Hole, 22-16 AWG, #4-#6 Stud, Insulated, Short Barrel, Electro-Tin Plated, 600 Volts Max.

Features: INSULUG Type YAE-Z Is Identical To Type YAE-N And Employs A Flanged Fork Tongue For Faster Installation While Maintaining Security If Supporting Screw Becomes Loose, 300 V Maximum, 105 DEG C Max, Flanged Fork: Permits Rapid, Easy Installation Of The Terminal Under The Screw Head Without Complete Removal Of The Screw, Additionally, It May Not Be Removed With Only A Slight Loosening Of The Screw, Tape Mounted Catalog Number: YAE18Z2M, Insulation Diameter (maximum): 0.125 IN, Package: Bulk, Color Code: Red, Wire Insulation Grip: Yes, Temperature Rating: 105 DEG C Maximum, Installation Tool: MR8-33T-1, M8ND Tool With One Of The Following Dies: N14HET-25V1, N10ET-9, N14HET-15, N10ET-23, Y10D, Y10-22 Tool, Finish: Electro-Tin Plated

## Product Details

### General

Application	Power Connector
Color Code	Red
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Flanged Fork
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	YAE-Z, Flanged
UPC	781810804155
UPC 12 Digit	7818108041555

### Dimensions

Dimension - B Length fraction	4/25 in
Dimension - B Length inch	0.16 in
Dimension - D inch	0.02 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Length Overall inch	1.00 in
Dimension - N inch	0.14 in
Dimension - Pad Width inch	0.28 in

Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#4;#5;#6
Dimension - Z inch	0.24 in

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - Copper Str Aircraft Size Range	AN22 - AN16
Conductor - Copper Str Size Range	22 AWG - 16 AWG
Conductor Type	CU C Str-Size

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>UL486</li> <li>Military Specified (Mil-Spec)</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>UL486</li> <li>Military Specified (Mil-Spec)</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1000
Packaging Type	Bulk

## For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)