

## YAEV8CRH

by Burndy  
Catalog ID: YAEV8CRH

Nylon-Insulated, Right-Angle Terminals-, 8, Max. Insul. Dia.: .30", Sleeve Color: Red, 8-10, 1.38 in L, .41 in W, 600 Volts Max.

Nylon-insulated right-angle terminals, made of seamless pure copper tubing



## Product Details

### General

Application	Designed to Accommodate Larger Conductor Insulation Diameters
Color Code	Red
Connector Type	Terminal
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, INSULUG
Trade Name	INSULUG™
Type	YAEV-RH
UPC	781810039755
UPC 12 Digit	7818100397555

### Dimensions

Dimension - B Length fraction	3/8 in
Dimension - B Length inch	0.38 in
Dimension - Bolt Hole Size inch	0.2 in
Dimension - D inch	0.66 in
Dimension - Hole Size inch	0.20 in
Dimension - Length Overall inch	1.38 in
Dimension - N inch	0.2 in
Dimension - Pad Width inch	0.41 in
Dimension - Strip Length inch	7/16
Dimension - Stud Size inch	#8;#9;#10
Dimension - Z inch	0.25 in
Physical Attribute - Tongue Angle	90 Degree

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - Copper Str Aircraft Size	AN 6
Conductor - Copper Str Aircraft Size Range	AN 6
Conductor - Copper Str Size	8
Conductor - Copper Str Size Range	8
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"><li>• UL486</li><li>• Military Specified (Mil-Spec)</li></ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"><li>• UL486</li><li>• Military Specified (Mil-Spec)</li></ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	500
-----------------------	-----

### For further technical assistance, please contact us

#### BURNDY Headquarters

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)