

# YAFW10NG

by Burndy  
Catalog ID: YAFW10NG

Four Way Connector, 10-12 AWG, 3 PC Nylon Insul, Yellow(Insul Color).

Package: 3 Piece/Box, Tongue Angle: Straight



## Product Details

### General

Application	Used to Connect multiple wires Quickly and securely
Color Code	Yellow
Connector Type	Four Way Connector
Insulation	Y
Insulation Type	3 Piece Nylon
Material	Copper
Physical Attribute - Tongue Type	Ring
Sub Brand	HYDENT
Temperature Rating	105°C
Trade Name	HYDENT™
Type	4-Way
UPC	781810525173
UPC 12 Digit	7818105251733

### Dimensions

Dimension - B Length fraction	1/4
Dimension - B Length inch	0.25 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Hole Size mm	4.00 mm
Dimension - Strip Length inch	5/16 in
Dimension - Stud Size inch	#8
Dimension - Z inch	0.28 in

### Electrical Ratings

Operating Voltage	600 V
-------------------	-------

### Conductor Related

Conductor Range	#12 AWG to #10 AWG
-----------------	--------------------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	50

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)