

YAFW10N

by Burndy
Catalog ID: YAFW10N

Four Way Connector, 10-12 AWG, Molded Nylon Insul, Yellow(Insul Color).
Tongue Angle: Straight



Product Details

General

Application	Used to Connect multiple wires Quickly and securely
Color Code	Yellow
Connector Type	Four Way Connector
Insulation	Y
Insulation Type	Molded Nylon
Material	Copper
Physical Attribute - Tongue Type	Ring
Sub Brand	HYDENT
Temperature Rating	105°C
Trade Name	HYDENT™
Type	4-Way
UPC	781810525166
UPC 12 Digit	7818105251666

Dimensions

Dimension - B Length fraction	1/4
Dimension - B Length inch	0.25 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Hole Size mm	4.00 mm
Dimension - Strip Length inch	5/16 in
Dimension - Stud Size inch	#8
Dimension - Z inch	0.28 in

Electrical Ratings

Operating Voltage	600 V
-------------------	-------

Conductor Related

Conductor Range	#12 AWG to #10 AWG
-----------------	--------------------

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)