

YAG1CTC14LD

by Burndy
Catalog ID: YAG1CTC14LD

Cu Compression terminal, Long barrel, #1 AWG Flex, 1/4" stud, 1 Hole, Lead plated



Product Details

General

Color Code	Green
Connector Type	Terminal
Die Index	11;375
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Lead Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Lead Plated
UPC	781810068939
UPC 12 Digit	7818100689399

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - D inch	0.64 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	62 mm
Dimension - Length Overall inch	2.44 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.47 in
Dimension - Pad Width inch	0.75 in
Dimension - Strip Length inch	1-7/16
Dimension - Thread Size	1/4 in
Dimension - Z inch	0.33 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	1 (225/#24) DLO
Conductor - Copper DLO Size Range	1 (225/#24) DLO
Conductor - Copper Flex G Size	1 AWG
Conductor - Copper Flex G Size Range	1 AWG
Conductor - Copper Flex H Size	1 AWG
Conductor - Copper Flex H Size Range	1 AWG
Conductor - Copper Flex I Size	1 AWG
Conductor - Copper Flex I Size Range	1 AWG
Conductor - Copper Flex K Size	1 AWG
Conductor - Copper Flex K Size Range	1 AWG
Conductor - Copper Flex M Size	1 AWG
Conductor - Copper Flex M Size Range	1 AWG
Conductor - Copper Str Navy Size	75 (37) Navy
Conductor - Copper Str Navy Size Range	75 (37) Navy
Conductor - Copper Str Size	1 AWG
Conductor - Copper Str Size Range	1 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	No

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)