

# YAG26LTC12LD

by Burndy  
Catalog ID: YAG26LTC12LD

Prop 65 Notice

Cu Compression terminal 2.38 inches long



## Product Details

### General

|                                      |                              |
|--------------------------------------|------------------------------|
| Color Code                           | Black                        |
| Connector Type                       | Terminal                     |
| Die Index                            | 13                           |
| Feature - Barrel Style               | Chamfered                    |
| Feature - Barrel Type                | Standard                     |
| Material                             | Copper                       |
| Physical Attribute - Number of Holes | 1                            |
| Physical Attribute - Tongue Type     | Standard                     |
| Plated                               | Y                            |
| Plating Type                         | Lead Plated                  |
| Temperature Rating                   | 194                          |
| Trade Name                           | HYLUG™                       |
| Type                                 | Standard Barrel, Lead Plated |
| UPC                                  | 781810036426                 |
| UPC 12 Digit                         | 7818100364266                |

### Dimensions

|                                   |         |
|-----------------------------------|---------|
| Dimension - B Length inch         | 0.81 in |
| Dimension - Bolt Hole Size inch   | 0.52 in |
| Dimension - Bolt Size fraction    | 1/2     |
| Dimension - D inch                | 1.08 in |
| Dimension - Hole Size inch        | 0.53 in |
| Dimension - Hole Size mm          | 13 mm   |
| Dimension - L Length Overall mm   | 61 mm   |
| Dimension - Length Overall inch   | 2.38 in |
| Dimension - N inch                | 0.53 in |
| Dimension - Outside Diameter inch | 0.63 in |
| Dimension - Pad Width inch        | 0.93 in |
| Dimension - Strip Length inch     | 13/16   |
| Dimension - Stud Size inch        | 1/2     |

|                                   |          |
|-----------------------------------|----------|
| Dimension - Z inch                | 0.55 in  |
| Physical Attribute - Tongue Angle | Straight |

## Electrical Ratings

|                          |       |
|--------------------------|-------|
| Rating - KVA             | 35 kV |
| Rating - Minimum Voltage | 600   |
| Voltage - Maximum        | 35000 |

## Conductor Related

|  |   |
|--|---|
| Conductor - Copper DLO Size            | 2/0 (375/#24) DLO                                 |
| Conductor - Copper Flex G Size         | 2/0 AWG   |
| Conductor - Copper Flex H Size         | 2/0 AWG   |
| Conductor - Copper Flex I Size         | 2/0 AWG   |
| Conductor - Copper Flex K Size         | 2/0 AWG   |
| Conductor - Copper Flex M Size         | 2/0 AWG   |
| Conductor - Copper Flex M Size Range   | 2/0 AWG   |
| Conductor - Copper Str Navy Size       | 125 (61) Navy                                     |
| Conductor - Copper Str Navy Size Range | 125 (61) Navy                                     |
| Conductor - Copper Str Size            | 2/0 AWG   |
| Conductor - Copper Str Size Range      | 2/0 AWG   |
| Conductor - CopperWeld Str Size        | 2/0 F AWG;2/0 G AWG;2/0 J AWG;2/0 K AWG;2/0 V AWG |
| Conductor - CopperWeld Str Size Range  | 2/0 F AWG-2/0 V AWG                               |
| Conductor - Material                   | Copper  |

## Certifications and Compliance

|                                    |              |
|------------------------------------|--------------|
| Certification - CSA Approved       | Yes          |
| Certification - ETL                | No           |
| Certification - UL Recognized      | No           |
| Certification - cULus              | No           |
| Industry Standard(s)               | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | NC           |
| UL Listed                          | Yes          |

## Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 200 |
|-----------------------|-----|

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)