

YAG27LNT875MMSL

by Burndy
Catalog ID: YAG27LNT875MMSL

Prop 65 Notice

Copper HYLUGTM , Single Hole W/O Insp Window, 3/0 AWG ,Orange, 14 Index,1-1/16" Strip Length,Tin plated



Product Details

General

Color Code	Orange
Connector Type	Terminal
Die Index	14
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810466520

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - L Length Overall mm	69 mm
Dimension - Length Overall inch	2.73 in
Dimension - N inch	0.33 in
Dimension - Outside Diameter inch	0.62 in
Dimension - Pad Width inch	0.76 in
Dimension - Strip Length inch	1-1/16
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size	3/0 AWG
Conductor - Copper Flex G Size Range	3/0 AWG
Conductor - Copper Flex H Size	3/0 AWG

Conductor - Copper Flex H Size Range	3/0 AWG
Conductor - Copper Flex I Size	3/0 AWG
Conductor - Copper Flex I Size Range	3/0 AWG
Conductor - Copper Flex K Size	3/0 AWG
Conductor - Copper Flex K Size Range	3/0 AWG
Conductor - Copper Flex M Size	3/0 AWG
Conductor - Copper Flex M Size Range	3/0 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)