



YAG28L2TC38LD

by Burndy
Catalog ID: YAG28L2TC38LD

Prop 65 Notice

Cu Tubing Hylug, 2 Holes w/o Inspection Window, 4/0 WELD, 4/0(550/#24) DLO, 4/0 AWG Code, 200 Navy, 600V-35kV, 3/8" stud, Standard, Compression, 0.40 in BCD

Product Details

General

Color Code	Purple
Connector Type	Terminal
Die Index	15
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Lead
Trade Name	HYLUG™
Type	Standard Barrel, Lead Plated
UPC	781810018361
UPC 12 Digit	7818100183611

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.03 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	88 mm
Dimension - Length Overall inch	3.46 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.77 in
Dimension - Pad Width inch	1.14 in
Dimension - Strip Length inch	1-1/16
Dimension - Z inch	0.43 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	4/0 (550/#24) DLO
Conductor - Copper Flex G Size	4/0 AWG
Conductor - Copper Flex H Size	4/0 AWG
Conductor - Copper Flex I Size	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
Conductor - Copper Flex M Size	4/0 AWG
Conductor - Copper Str Navy Size	200 (61) Navy
Conductor - Copper Str Size	4/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)