

# YAG28RSB1

by Burndy  
Catalog ID: YAG28RSB1

Cu Tubing Compression Terminal, 1 Hole, 4/0 AWG, 211.6 kcmil Nom., 90 Deg Bent, Belled End



## Product Details

### General

Color Code	Green
Connector Type	Terminal
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Belled Barrel, Tin Plated
UPC	781810184417
UPC 12 Digit	7818101844177

### Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.21 in
Dimension - Hole Size inch	0.54 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	55 mm
Dimension - Length Overall inch	2.17 in
Dimension - N inch	0.56 in
Dimension - Outside Diameter inch	0.77 in
Dimension - Pad Width inch	1.12 in
Physical Attribute - Tongue Angle	90 Degree

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	4/0 AWG
-----------------------------	---------

Conductor - Material	Copper
----------------------	--------

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	50
-----------------------	----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)