

YAG28TC516DTLDYEL

by Burndy
Catalog ID: YAG28TC516DTLDYEL

Lead Plated Sealed Barrel Battery Lug, 4/0(550/#24)DLO, 225 Amps,
5/16" stud, Yellow, 16 Index



Product Details

General

Color Code	Yellow
Connector Type	Terminal
Die Index	16
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Lead
Trade Name	HYLUG™
Type	Long Barrel, Lead Plated
UPC	781810184448
UPC 12 Digit	7818101844488

Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.63 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - Inside Diameter inch	0.63 in
Dimension - L Length Overall mm	74 mm
Dimension - Length Overall inch	2.93 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.77 in
Dimension - Pad Width inch	1.14 in
Dimension - Strip Length inch	1-11/16
Dimension - Z inch	0.36 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	4/0 (550/#24) DLO
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)