

YAG2CLTC38LD

by Burndy
Catalog ID: YAG2CLTC38LD

Prop 65 Notice

Cu Tubing Hylug; 1 Hole w/o Inspection Window; #2 AWG Flex,60 Navy; 600V-35kV; 3/8" stud; Standard; Compression; 0.40 in BCD



Product Details

General

Color Code	Brown
Connector Type	Terminal
Die Index	10
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Straight
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Lead Plated
UPC	781810034651
UPC 12 Digit	7818100346511

Dimensions

Dimension - B Length fraction	5/8
Dimension - B Length inch	0.63 in
Dimension - Bolt Hole Size inch	0.40 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.83 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.68 in
Dimension - Strip Length inch	11/16 in
Dimension - Stud Size inch	3/8 in
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	2 (125/24) DLO ; 2 (150/24) DLO
Conductor - Copper Flex G Size	2 AWG
Conductor - Copper Flex H Size	2 AWG
Conductor - Copper Flex I Size	2 AWG
Conductor - Copper Flex K Size	2 AWG
Conductor - Copper Flex M Size	2 AWG
Conductor - Copper Solid Size	2 AWG
Conductor - Copper Str Navy Size	60 NAVY
Conductor - Copper Str Size	2 AWG
Conductor - CopperWeld Str Size	2 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)