



YAG32L2NTCLD

by Burndy
Catalog ID: YAG32L2NTCLD

Cu Tubing HYLUG™, 2 Holes, Lead Plated

Product Details

General

Color Code	Red
Connector Type	Terminal
Die Index	18
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Lead Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Lead Plated
UPC	781810036280
UPC 12 Digit	7818100362800

Dimensions

Dimension - B Length inch	1.19 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.03 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	125 mm
Dimension - Length Overall inch	4.91 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	1.40 in
Dimension - Strip Length inch	1-1/4
Dimension - Z inch	0.65 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	313.1 (775/#24) DLO
Conductor - Copper Flex G Size	300 kcmil
Conductor - Copper Flex H Size	300 kcmil
Conductor - Copper Flex I Size	300 kcmil
Conductor - Copper Flex K Size	300 kcmil
Conductor - Copper Flex M Size	300 kcmil
Conductor - Copper Flex M Size Range	300 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	204
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)