

YAG36LTC12LD

by Burndy
Catalog ID: YAG36LTC12LD

Prop 65 Notice

Copper Tubing HYLUG™, 444.4 kcmil (1100/24), 20 or 299 Index, Standard Barrel



Product Details

General

Color Code	Brown
Connector Type	Terminal
Die Index	20;299
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Lead
Trade Name	HYLUG™
Type	Standard Barrel, Lead Plated
UPC	781810038673
UPC 12 Digit	7818100386733

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	5/8
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	85 mm
Dimension - Length Overall inch	3.34 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.73 in
Dimension - Strip Length inch	1-3/8 in
Dimension - Stud Size inch	5/8
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	444.4 kcmil; (1100/24)
Conductor - Copper Flex G Size	450 kcmil
Conductor - Copper Flex H Size	450 kcmil
Conductor - Copper Flex I Size	450 kcmil
Conductor - Copper Flex K Size	450 kcmil
Conductor - Copper Flex M Size	450 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)