



## YAG38L2NT38LD

by Burndy  
Catalog ID: YAG38L2NT38LD

Prop 65 Notice

Cu Tubing Hylug, 2 Holes, 535.3 kcmil, 1/2" Stud

### Product Details

#### General

Color Code	Pink
Connector Type	Terminal
Die Index	L99
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Lead
Trade Name	HYLUG™
Type	Standard Barrel, Lead Plated
UPC	781810270738
UPC 12 Digit	7818102707388

#### Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.45 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	112 mm
Dimension - Length Overall inch	4.40 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Pad Width inch	1.63 in
Dimension - Strip Length inch	1-7/16 in
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.53 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size	535.3 kcmil; (1325/24)
Conductor - Copper Flex G Size	500 kcmil
Conductor - Copper Flex H Size	500 kcmil
Conductor - Copper Flex I Size	500 kcmil
Conductor - Copper Flex K Size	500 kcmil
Conductor - Copper Flex M Size	450 kcmil
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	Yes

## Logistics

Minimum Pack Quantity	200
-----------------------	-----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)