



YAG38L2NTCLD

by Burndy
Catalog ID: YAG38L2NTCLD

Prop 65 Notice

Copper Compression Lug, 2 Hole w/o Inspection Window, 535.3 Flex, 1/2" Stud, 1-3/4" Stud Hole Spacing, Short Barrel, Lead Plated.

Features: Compression Terminal, Finish: Lead Plated, Tongue Angle: Straight, Die Index: L99, Strip Length: 1-7/16 IN

Product Details

General

Application	For Flex Conductors
Color Code	Pink
Connector Type	Terminal
Die Index	L99
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Lead
Sub Brand	HYLUG,TERMINALS
Trade Name	HYLUG™
Type	Standard Barrel, Lead Plated
UPC	781810020944
UPC 12 Digit	7818100209444

Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.45 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	137 mm
Dimension - Length Overall inch	5.40 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Pad Width inch	1.82 in
Dimension - Strip Length inch	1-7/16 in
Dimension - Stud Size inch	1/2

Dimension - Z inch	0.65 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	535.3 kcmil; (1325/24)
Conductor - Copper Flex G Size	500 kcmil
Conductor - Copper Flex H Size	500 kcmil
Conductor - Copper Flex I Size	500 kcmil
Conductor - Copper Flex K Size	500 kcmil
Conductor - Copper Flex M Size	450 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)