



YAG38L2TC516LD

by Burndy
Catalog ID: YAG38L2TC516LD

Cu Tubing Hylug, 2 Holes, 535.3 kcmil, 5/16" Stud

Product Details

General

Color Code	Pink
Connector Type	Terminal
Die Index	L99
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Lead
Trade Name	HYLUG™
Type	Standard Barrel, Lead Plated
UPC	781810320471
UPC 12 Digit	7818103204711

Dimensions

Dimension - B Length fraction	1-4/9 in
Dimension - B Length inch	1.45 in
Dimension - Bolt Size fraction	5/16
Dimension - Hole Size fraction	1/3
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	104 mm
Dimension - Length Overall inch	4.09 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Pad Width inch	1.82 in
Dimension - Strip Length inch	1-7/16 in
Dimension - Stud Size inch	5/16
Dimension - Z inch	0.37 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	535.3 kcmil; (1325/24)
Conductor - Copper Flex G Size	500 kcmil
Conductor - Copper Flex H Size	500 kcmil
Conductor - Copper Flex I Size	500 kcmil
Conductor - Copper Flex K Size	500 kcmil
Conductor - Copper Flex M Size	500 kcmil
Conductor - Material	Copper

Certifications and Compliance

Standards - RoHS Compliance Status	NC
------------------------------------	----

Logistics

Minimum Pack Quantity	204
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)