

YAG40LTC38FX

by Burndy
Catalog ID: YAG40LTC38FX

Prop 65 Notice

Copper Compression Terminal



Product Details

General

Color Code	Black
Connector Type	Terminal
Die Index	24
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810194348
UPC 12 Digit	7818101943488

Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.42 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	87 mm
Dimension - Length Overall inch	3.42 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.35 in
Dimension - Pad Width inch	1.96 in
Dimension - Strip Length inch	1-7/16 in
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.52 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	646 kcmil; (1600/24)
Conductor - Copper Flex G Size	650 kcmil
Conductor - Copper Flex H Size	650 kcmil
Conductor - Copper Flex I Size	650 kcmil
Conductor - Copper Flex K Size	650 kcmil
Conductor - Copper Flex M Size	650
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	150
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)