



YAG44L2TC12LD

by Burndy
Catalog ID: YAG44L2TC12LD

Prop 65 Notice

Cu Tubing Hylug, 2 Holes, #4 Weld, #4 AWG, 1/2" Stud

Product Details

General

Color Code	Yellow
Connector Type	Terminal
Die Index	L115
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Lead
Trade Name	HYLUG™
Type	Standard Barrel, Lead Plated
UPC	781810038666
UPC 12 Digit	7818100386666

Dimensions

Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	1.65 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	130 mm
Dimension - Length Overall inch	5.11 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	2.18 in
Dimension - Strip Length inch	1-5/8 in
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.56 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	777.7 kcmil; (1925/24)
Conductor - Copper Flex G Size	750 kcmil
Conductor - Copper Flex H Size	750 kcmil
Conductor - Copper Flex I Size	750 kcmil
Conductor - Copper Flex K Size	750 kcmil
Conductor - Copper Flex M Size	750
Conductor - Copper Str Size	750 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)