

# YAG4CLTC14BR

by Burndy  
Catalog ID: YAG4CLTC14BR

4FLEX 1/4STUD UNPLT



## Product Details

### General

Color Code	Gray
Connector Type	Terminal
Die Index	8
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Bright
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Lead Plated
UPC	781810449189
UPC 12 Digit	7818104491899

### Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - D inch	0.64 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.48 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Pad Width inch	0.55 in
Dimension - Strip Length inch	1/2
Dimension - Z inch	0.33 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size	4 (105/#24) DLO
Conductor - Copper DLO Size Range	4 (105/#24) DLO
Conductor - Copper Flex G Size	4 AWG
Conductor - Copper Flex G Size Range	4 AWG
Conductor - Copper Flex H Size	4 AWG
Conductor - Copper Flex H Size Range	4 AWG
Conductor - Copper Flex I Size	4 AWG
Conductor - Copper Flex I Size Range	4 AWG
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Flex K Size Range	4 AWG
Conductor - Copper Flex M Size	4 AWG
Conductor - Copper Flex M Size Range	4 AWG
Conductor - Copper Str Navy Size	40 (19) Navy;50 (19) Navy
Conductor - Copper Str Navy Size Range	40 (19) Navy-50 (19) Navy
Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor - CopperWeld C Solid Size	4 AWG
Conductor - CopperWeld Solid Size Range	4 AWG
Conductor - CopperWeld Str Size	4 A AWG;4 D AWG;4 N AWG;4 P AWG
Conductor - CopperWeld Str Size Range	4 A AWG-4 P AWG
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	50
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)