



## YAG4CLTC14FX90G2

by Burndy  
Catalog ID: YAG4CLTC14FX90G2

Cu Tubing Hylug, 1 Hole, #4 Flex, #4 AWG, 1/4 Stud

### Product Details

#### General

Color Code	Gray
Connector Type	Terminal
Die Index	8
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810440971
UPC 12 Digit	7818104409711

#### Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.14 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Pad Width inch	.55 in
Dimension - Strip Length inch	1/2 in
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	90 Degree

#### Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size	4 (105/#24) DLO
Conductor - Copper Flex G Size	4 AWG
Conductor - Copper Flex H Size	4 AWG
Conductor - Copper Flex I Size	4 AWG
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Flex M Size	4 AWG
Conductor - Copper Str Navy Size	40 & 50
Conductor - Copper Str Size	4 AWG
Conductor - CopperWeld C Solid Size	4 AWG
Conductor - CopperWeld Str Size	4 AWG
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)