

YAG6CLTC10LD

by Burndy
Catalog ID: YAG6CLTC10LD

Prop 65 Notice

One hole Cu Compression terminal, Standard barrel, 6 AWG FLEX, #10 stud, Lead plated



Product Details

General

Color Code	Blue
Connector Type	Terminal
Die Index	7;374
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Lead
Trade Name	HYLUG™
Type	Standard Barrel, Lead Plated
UPC	781810321430
UPC 12 Digit	7818103214300

Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	.50 in
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.21 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.3 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	.31 in
Dimension - Pad Width inch	.48 in
Dimension - Strip Length inch	1/2 in
Dimension - Stud Size inch	#10
Dimension - Z inch	0.27 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	6(61/#24) DLO
Conductor - Copper DLO Size Range	6 (61/#24) DLO
Conductor - Copper Flex G Size	6 AWG
Conductor - Copper Flex G Size Range	6 AWG
Conductor - Copper Flex H Size	6 AWG
Conductor - Copper Flex H Size Range	6 AWG
Conductor - Copper Flex I Size	6 AWG
Conductor - Copper Flex I Size Range	6 AWG
Conductor - Copper Flex K Size	6 AWG
Conductor - Copper Flex K Size Range	6 AWG
Conductor - Copper Flex M Size	6 AWG
Conductor - Copper Flex M Size Range	6 AWG
Conductor - Copper Solid Size	6 AWG
Conductor - Copper Solid Size Range	6 AWG
Conductor - Copper Str Navy Size	30
Conductor - Copper Str Size	6 AWG
Conductor - CopperWeld C Solid Size	6 AWG
Conductor - CopperWeld Solid Size Range	6 AWG
Conductor - CopperWeld Str Size	6 AWG
Conductor - CopperWeld Str Size Range	6 A AWG-6 D AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)