



## YAG8CL1LD

by Burndy  
Catalog ID: YAG8CL1LD

One hole Cu Compression terminal, Standard barrel, Without Inspection Window, Lead Plated

### Product Details

#### General

|                        |                              |
|------------------------|------------------------------|
| Connector Type         | Terminal                     |
| Feature - Barrel Style | Chamfered                    |
| Feature - Barrel Type  | Standard                     |
| Material               | Copper                       |
| Plated                 | Y                            |
| Plating Type           | Lead                         |
| Temperature Rating     | 194                          |
| Type                   | Standard Barrel, Lead Plated |
| UPC 12 Digit           | 0                            |

#### Dimensions

|                                   |          |
|-----------------------------------|----------|
| Physical Attribute - Tongue Angle | Straight |
|-----------------------------------|----------|

#### Electrical Ratings

|                          |       |
|--------------------------|-------|
| Rating - KVA             | 35 kV |
| Rating - Minimum Voltage | 600   |
| Voltage - Maximum        | 35000 |

#### Conductor Related

|                                   |        |
|-----------------------------------|--------|
| Conductor - Copper DLO Size Range | N/A    |
| Conductor - Material              | Copper |

#### Certifications and Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | Yes |
| Certification - ETL                | No  |
| Certification - UL Recognized      | No  |
| Certification - cULus              | No  |
| Standards - RoHS Compliance Status | NC  |
| UL Listed                          | Yes |

#### Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 200 |
|-----------------------|-----|

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)