

# YAG8CLTC38LD

by Burndy  
Catalog ID: YAG8CLTC38LD

Prop 65 Notice

One hole Cu Compression terminal, Standard barrel, Without Inspection Window, 8 AWG Flex, 3/8" stud, Lead Plated



## Product Details

### General

Color Code	Red
Connector Type	Terminal
Die Index	49
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Lead
Trade Name	HYLUG™
Type	Standard Barrel, Lead Plated
UPC	781810034583
UPC 12 Digit	7818100345833

### Dimensions

Dimension - B Length fraction	7/16 in
Dimension - B Length inch	0.44 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - D inch	0.83 in
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	47 mm
Dimension - Length Overall inch	1.86 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.58 in
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.42 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size	8 (37/#24) DLO
Conductor - Copper Flex G Size	8 AWG
Conductor - Copper Flex H Size	8 AWG
Conductor - Copper Flex I Size	8 AWG
Conductor - Copper Flex K Size	8 AWG
Conductor - Copper Flex M Size	8 AWG
Conductor - Copper Str Navy Size	23 (7) Navy
Conductor - Copper Str Size	8 AWG
Conductor - CopperWeld C Solid Size	8 AWG
Conductor - CopperWeld Solid Size Range	8 AWG
Conductor - CopperWeld Str Size	8 A AWG;8 C AWG;8 D AWG
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC
UL Listed	Yes

## Logistics

Minimum Pack Quantity	200
-----------------------	-----

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)