

YAGB25LTC14FXOEM

by Burndy
Catalog ID: YAGB25LTC14FXOEM

Cu Tubing Hylug, 1/0 AWG, 1/4 IN Stud



Product Details

General

Application	Power Connector
Connector Type	Terminal
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810547427
UPC 12 Digit	7818105474277

Dimensions

Dimension - Bolt Hole Size inch	0.25 in
Dimension - Bolt Size fraction	1/4
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.92 in
Dimension - Pad Width inch	0.83 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	1/0
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)