

# YAGB26LTC12FXOEM

by Burndy  
Catalog ID: YAGB26LTC12FXOEM

Cu Tubing Hylug, 2/0 AWG, 1/2 IN Stud



## Product Details

### General

Application	Power Connector
Connector Type	Terminal
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810525975
UPC 12 Digit	7818105259755

### Dimensions

Dimension - Bolt Hole Size inch	0.50 in
Dimension - Bolt Size fraction	1/2
Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.38 in
Dimension - Pad Width inch	0.93 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	2/0
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)