

YAGB26LTC14FXOEM

by Burndy
Catalog ID: YAGB26LTC14FXOEM

Cu Battery Terminal Lug Type, 2/0 AWG, 1/4 in Stud, Connector Color Code- Orange, Die Color Code- Black, 1-Hole, Tin Plated, Terminal, Standard Barrel



Product Details

General

Application	Power Connector
Color Code	Orange
Connector Type	Terminal
Die Index	13
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electroplated
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810525982
UPC 12 Digit	7818105259822

Dimensions

Dimension - L Length Overall mm	50 mm
Dimension - Length Overall inch	1.95 in
Dimension - Strip Length inch	1-3/16 in
Dimension - Stud Size inch	1/4 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	2/0 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)