



# YAGB28LTC12FX90RTOEM

by Burndy  
Catalog ID: YAGB28LTC12FX90RTOEM

Prop 65 Notice

Cu Battery Terminal Lug Type, 4/0 AWG, 1/2 in Stud, 1-Hole, Tin Plated, Terminal, Standard Barrel

## Product Details

### General

Application	Power Connector
Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electroplated
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810512142
UPC 12 Digit	7818105121422

### Dimensions

Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.58 in
Dimension - Stud Size inch	1/2 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes

UL Listed	No
-----------	----

**Logistics**

Minimum Pack Quantity	200
-----------------------	-----

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)