

YAGB28LTC14FXOEM

by Burndy
Catalog ID: YAGB28LTC14FXOEM

Cu Tubing Hylug, 4/0 AWG, 1/4 IN Stud



Product Details

General

Application	Power Connector
Connector Type	Terminal
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810531082
UPC 12 Digit	7818105310822

Dimensions

Dimension - L Length Overall mm	63 mm
Dimension - Length Overall inch	2.48 in
Dimension - Pad Width inch	1.14 in
Dimension - Stud Size inch	1/4 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	4/0
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)