



## YAGB28LTC38FX

by Burndy  
Catalog ID: YAGB28LTC38FX

Cu Battery Terminal Lug Type, 4/0 AWG, Purple, 15 Index, 3/8 IN Stud, 1-3/16 IN Strip Length

### Product Details

#### General

Application	Power Connector
Color Code	Yellow
Connector Type	Terminal
Die Index	15
Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810562925
UPC 12 Digit	7818105629255

#### Dimensions

Dimension - L Length Overall mm	65 mm
Dimension - Length Overall inch	2.56 in
Dimension - N inch	0.55 in
Dimension - Outside Diameter inch	.78 In
Dimension - Pad Width inch	1.10 in
Dimension - Strip Length inch	1-3/16 in
Dimension - Stud Size inch	3/8 in
Dimension - Z inch	0.48 in

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

#### Conductor Related

Conductor - Copper Str Size	4/0
Conductor Type	CU C Str-Size

#### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	200 EA
Minimum Pack Quantity	20

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)