

# YAGB2CLTC10FXOEM

by Burndy  
Catalog ID: YAGB2CLTC10FXOEM

1 Hole HYLUG™ Cu Battery Terminal, #2 AWG, #10 stud, 2.09" L, 0.81" W, Green



## Product Details

### General

Application	Power Connector
Connector Type	Terminal
Physical Attribute - Number of Holes	1
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810563120
UPC 12 Digit	7818105631200

### Dimensions

Dimension - L Length Overall mm	53 mm
Dimension - Length Overall inch	2.09 in
Dimension - Pad Width inch	0.81 in
Dimension - Strip Length inch	15/16 in
Dimension - Stud Size inch	#10

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Flex G Size	2 AWG
Conductor - Copper Flex H Size	2 AWG
Conductor - Copper Flex I Size	2 AWG
Conductor - Copper Flex K Size	2 AWG
Conductor - Copper Str Size	2 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

## Logistics

Minimum Pack Quantity	200
-----------------------	-----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)