

YAGB4CLTC12FXOEM

by Burndy
Catalog ID: YAGB4CLTC12FXOEM

1 Hole HYLUG™ Cu Battery Terminal, 4 AWG, 1/2" stud, 1.97" L, 0.75" W, Grey



Product Details

General

Application	Power Connector
Connector Type	Terminal
Physical Attribute - Number of Holes	1
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810563113
UPC 12 Digit	7818105631133

Dimensions

Dimension - L Length Overall mm	50 mm
Dimension - Length Overall inch	1.97 in
Dimension - Pad Width inch	0.75 in
Dimension - Strip Length inch	15/16 in
Dimension - Stud Size inch	1/2 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size	4 AWG
Conductor - Copper Flex H Size	4 AWG
Conductor - Copper Flex I Size	4 AWG
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Str Size	4 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)