



YAGB4CLTC14FX

by Burndy
Catalog ID: YAGB4CLTC14FX

1 Hole HYLUG Cu Battery Terminal, #4 AWG, 1/4" stud, 1.97" L, 0.75" W, Gray

Product Details

General

Application	Power Connector
Color Code	Gray
Connector Type	Terminal
Die Index	6
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810562734
UPC 12 Digit	7818105627344

Dimensions

Dimension - L Length Overall mm	50 mm
Dimension - Length Overall inch	1.97 in
Dimension - Strip Length inch	15/16 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	200 EA
Minimum Pack Quantity	20

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)